

OPEN SUN 1050

ULTRA PERFORMANCE



HIGHLIGHTS

- ULTRA PERFORMANCE
- FAN COOLING PLUS
- MULTI RELAX ACRYLIC
- INTERIOR TOUCH DISPLAY



Ergoline

OPEN SUN 1050 | ULTRA PERFORMANCE



The Open Sun by Ergoline is the only unit of its kind offering 360-degree high-pressure tanning in an open environment. One of Ergoline's all-time best-selling units, the Open Sun 1050 is a proven performer and a perfect addition to your equipment mix, giving your customers beautiful bronzing results in 12 minutes or less. Featuring proprietary filter glass technology and 30 high-pressure lamps perfectly aligned along the canopy and base, this unit is truly a work of art. An open-air design and Fan Cooling Plus ensure customers' relaxation during a session. This unit will draw customers from near and far and is a true masterpiece for any salon.

ERGOLINE, A BRAND OF JK PRODUCTS & SERVICES, INC.

411 West Washington Avenue, Suite B | Jonesboro, AR 72401

☎ Toll-free: 888.771.0996 | www.ergoline.us

CONTRAINDICATIONS:

Follow Instructions. Avoid over-exposure as with natural sunlight. Over-exposure can cause eye or skin injury and allergic reactions. Repeated exposure may cause premature aging of the skin and skin cancer. ALWAYS WEAR PROTECTIVE EYEWEAR! Failure to do so may result in severe burns or long term injury to the eyes. Certain medications or cosmetics may increase your sensitivity to ultraviolet radiation. Consult a physician before using sunlamps if you are using medication, have a history of skin problems or believe yourself to be especially sensitive to sunlight. If you do not tan in the sun, you are unlikely to tan from the use of this product. Please refer to the recommended exposure schedule for your skin type and do not tan more than once in a 24-hour period. Attention: This sunlamp product should not be used on persons under the age of 18 years. Persons who should not use this device include anyone who is sunburned, has open wounds, is naturally pale, has discolored patches of skin, has an increased risk of skin cancer, is being treated for or taking medicine causing photosensitivity, is pregnant, has atypical moles or more than 16 moles on their body (2mm diameter or larger). © 2020 JK Products & Services, Inc.

PERFORMANCE	Session Time	12 minutes
	Technology	Ultra Performance
	Low pressure lamps	27 X 580 W
	Facial tanner	3 X 640 W Ultra Performance Plus
	Spaghetti lamps	-
COMFORT	Shoulder Tan	-
	Air conditioning	-
	Ventilation	Fan Cooling Plus
	Aqua Fresh / Aroma	-
	Sound	Stereo Sound
HANDLING	Smart phone connection	MP3 AUX
	Acrylic	Multi Relax
	External display	-
	Internal display	✓
	NFC Connect	-
DESIGN	Voice Guide	-
	Set-up Manager	-
	Miscellaneous	-
TECHNICAL SPECIFICATIONS	External lighting	Exterior Lighting
	Internal lighting	Interior Lighting
	Dimensions closed	97-5/8 x 75-3/16 x 64-3/8
	Dimensions open (L x W x H in)	97-5/8 x 75-3/16 x 78-9/16
	Minimum Recommended Room Size (L x W ft)	10 x 9
ELECTRICAL SPECIFICATIONS	Unit Footprint (L x W in)	106-5/6 x 106-5/16
	Max. power consumption with 400/415 V 3N power supply with 230 V 1N power supply	21,500 W
	Fuse (delayed action)	70 amp 3 Ø 130 amp single Ø
	Weight	2,062 lb
	Rated frequency	60 Hz
	Rated voltage	230 V
	Rated amp draw 3 Ø	58
	Rated amp draw 1 Ø	98
	Mains Power Connection	The unit is configured from the factory for connection to 3-Phase power. A 1" liquid-tight connector is provided. *Owner is responsible for all wiring up to the terminal block connection inside the device. As well as ensuring the wire is properly sized for the amp draw and breaker selection per the electrical code in their area.
	Load on the acrylic panel	max. 330 lbs.
	Operating Temperature	59-89 (degrees) F
	Number of body lamps	27 @ 580 W