


SUN ANGEL DUO 1400

INDIVIDUAL PERFORMANCE




HIGHLIGHTS

- ESSENTIAL & STYLING SUNSHINE
- SENSORED CONTROLLED TANNING
- TEMPTRONIC
- 3D SOUND

SUNANGEL

SUN ANGEL DUO 1400 | INDIVIDUAL PERFORMANCE



The SUNANGEL was originally introduced in 2007 as the only tanning unit of its' kind to feature patented skin sensor technology, and now, more than a decade later, the SUNANGEL continues to represent the very best technology the industry has to offer. By creating a custom tanning session for every customer and utilizing sensor technology, the SUNANGEL virtually eliminates the risk of over-exposure. All the while creating beautiful results for an increasingly wide range of customers and skin tones. The LED Light Show creates beautiful animations in sunny colors, highlighting the dramatic lines of the bed.

SUN ANGEL, A BRAND OF JK PRODUCTS & SERVICES, INC.

411 West Washington Avenue, Suite B | Jonesboro, AR 72401

Toll-free: 888.771.0996 | www.ergoline.us

PERFORMANCE	Session Time	12 minutes
	Technology	Individual Performance
	Low pressure lamps	38 x 200 W Type A 14 x 200 W Type B
	Facial tanner	4 x 520 W
	Spaghetti lamps	3 x 8 W Type B
	Shoulder Tan	2 x 250 W
COMFORT	Air conditioning	Tempronic Plus
	Ventilation	Comfort Cooling
	Aqua Fresh / Aroma	✓/✓
	Sound	3D Sound System
	Smart phone connection	MP3 AUX
	Acrylic	Body Form Plus
HANDLING	External display	-
	Internal display	✓
	NFC Connect	✓
	Voice Guide	✓
	Set-up Manager	Professional Set-Up Manager
	Miscellaneous	-
DESIGN	External lighting	LED Light Show
	Internal lighting	LED Interior Light
TECHNICAL SPECIFICATIONS	Dimensions closed	93-5/16 x 53-13/16 x 52-1/16
	Dimensions open (L x W x H in)	93-5/16 x 53-13/16 x 66-11/16
	Minimum Recommended Room Size (L x W ft)	10 x 9
	Unit Footprint (L x W in)	94-1/2 x 82-11/16
	Max. power consumption with 400/415 V 3N power supply with 230 V 1N power supply	13,200 W
	Fuse (delayed action)	50 amp 3 Ø 80 amp single Ø
ELECTRICAL SPECIFICATIONS	Weight	1,211 lb
	Rated frequency	60 Hz
	Rated voltage	230 V
	Rated amp draw 3 Ø	31
	Rated amp draw 1 Ø	52
	Mains Power Connection	The unit is configured from the factory for connection to 3-Phase power. A 1" liquid-tight connector is provided. *Owner is responsible for all wiring up to the terminal block connection inside the device. As well as ensuring the wire is properly sized for the amp draw and breaker selection per the electrical code in their area.
	Load on the acrylic panel	max. 330 lbs.
	Operating Temperature	59-89 (degrees) F
	Number of body lamps	48 @ 200W 2M

CONTRAINDICATIONS:

Follow Instructions. Avoid over-exposure as with natural sunlight. Over-exposure can cause eye or skin injury and allergic reactions. Repeated exposure may cause premature aging of the skin and skin cancer. ALWAYS WEAR PROTECTIVE EYEWEAR! Failure to do so may result in severe burns or long term injury to the eyes. Certain medications or cosmetics may increase your sensitivity to ultraviolet radiation. Consult a physician before using sunlamps if you are using medication, have a history of skin problems or believe yourself to be especially sensitive to sunlight. If you do not tan in the sun, you are unlikely to tan from the use of this product. Please refer to the recommended exposure schedule for your skin type and do not tan more than once in a 24-hour period. Attention: This sunlamp product should not be used on persons under the age of 18 years. Persons who should not use this device include anyone who is sunburned, has open wounds, is naturally pale, has discolored patches of skin, has an increased risk of skin cancer, is being treated for or taking medicine causing photosensitivity, is pregnant, has atypical moles or more than 16 moles on their body (2mm diameter or larger). © 2020 JK Products & Services, Inc.